

No-Clean Halogen-Free Tack Flux in 10cc Syringe w/ plunger & tip

Product Highlights

- Halogen-Free
 - Ideal for all rework, solder, de-solder and reflow applications
 - Non-corrosive, non-conductive, no-clean
 - Tack flux will not run all over PCB when applied
 - Has a pleasant odor
 - Excellent wetting
 - Easily cleaned with isopropyl alcohol (IPA)
 - Attachment of BGA spheres
 - Soldering flip chip components
 - Long stencil life
 - Wide process window
 - Clear residue
 - Can be used with Leaded and Lead-Free applications
- RoHS 3 and REACH compliant**



Specifications

- | | |
|----------------------|---|
| Flux Type: | Synthetic No-Clean Halogen-Free (for Leaded and Lead-Free applications) |
| Flux Classification: | ROL0 |
| Packaging: | 10cc/10g Syringe |
| Shelf Life: | Refrigerated >24 months, Unrefrigerated >24 months |

Stencil Life

- >8 hours @ 20-50% RH 22-28°C (72-82°F)
- >4 hours @ 50-70% RH 22-28°C (72-82°F)

Stencil Cleaning

Automated stencil cleaning systems for both stencil and misprinted boards. Manual cleaning using isopropyl alcohol (IPA).

Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). Do not freeze. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.

Conforms to the following Industry Standards:

- | | |
|--|-----|
| J-STD-004B, Amendment 1 (Solder Fluxes): | Yes |
| RoHS 3 Directive (EU) 2015/863: | Yes |